

Philips
External Drive

DVD

18x ReWriter

SPD3400CC



DVD, RAM and CD in one

The name to trust reliability & compatibility

The Philips external DVD RW drive reads and writes DVD, RAM, Dual layer and CD formats. It simply plugs into a USB port, and can be used with several PCs. And coming from the co-inventor of DVD media, you can be sure it's ultra reliable.

Witness the latest technology

- Double layer writer for +R and -R, DL media
- DVD RAM enlarging your storage capacity
- 8.5GB storage capacity on a single sided double layer disc

Superior Performance

- 18x writing speed
- 8x writing on DVD+R DL

Extreme Reliability and Robustness

- Dynamic Calibration ensure writing quality at high DVD speed
- Safe and reliable rewriting with Seamless Link
- Best writing quality at high DVD speed

PHILIPS
sense and simplicity

Specifications

Writing Speed

- **CD-R:** 48x (7200KB/sec) by CAV
- **DVD+R:** 18x (21600KB/sec) maximum by CAV
- **DVD+R DL:** 4X (5400KB/sec) by CLV
- **DVD-R:** 18x (21600KB/sec) maximum by CAV
- **DVD-R DL:** 8x (5400KB/sec) maximum by CLV
- **DVD-RAM:** 12x (6750KB/sec) maximum by PCAV

Rewriting Speed

- **CD-RW:** 24X (3600KB/sec) by CAV
- **DVD+RW:** 8X (10800KB/sec) by ZCLV
- **DVD-RW:** 6X (8100KB/sec) by ZCLV

Reading Speed

- **Access time:** 160ms
- **Buffer size:** 2MB
- **CD-R:** 48X (7200KB/sec) by CAV
- **DVD ROM:** 16X (21600KB/sec) by CAV

Connectivity

- **Interface:** USB 2

System Requirements

- **Hard disc space:** 650MB
- **PC OS:** Windows 98 SE, 2000, ME, XP
- **Processor:** Pentium 4 1 GHz or faster
- **RAM memory:** 128 MB

Software

- **Ahead Nero Suite 6:** InCD 4, Nero Burning Rom 6, Nero Vision express 2

Dimensions

- **Product dimensions (WxDxH):** 145 x 170 x 42 mm
- **Product weight:** 0.9 kg

Packaging Data

- **I2NC:** 908210006799
- **Gross weight:** 2.3 kg

- **Height:** 242 mm
- **Length:** 304 mm
- **Width:** 146 mm

Technical specifications

- **EMC standards:** EN55022, EMS55024, FCC Part 15
- **Safety standards:** EN60950, EN60825, UL1950
- **Humidity:** 15 - 80 %RH (no condensation)
- **Operating temperature range:** 5 - 50 °C
- **Storage temperature range:** -40 - 65 °C

Inner Carton

- **I2NC:** 9082 100 06799
- **Gross weight:** 2.3 kg
- **Height:** 242 mm
- **Length:** 304 mm
- **Quantity:** 1
- **Width:** 146 mm
- **EAN/UPC/GTIN:** 87 12581 34049 0

Outer Carton

- **I2NC:** 908210006799
- **Gross weight:** 9.925 kg
- **Height:** 324 mm
- **Length:** 517 mm
- **Quantity:** 4
- **Width:** 324 mm
- **EAN/UPC/GTIN:** 87 12581 34050 6

Outer Carton two

- **Quantity:** 144

Convenience

- **Ease of installation:** Plug & Play
- **Ease of Use:** How to manual, step by step

Power

- **Adaptor type:** DC 5V/12V
- **Power consumption:** 25 W

Product highlights

Dynamic Calibration

Dynamic Calibration optimizes DVD writing quality of high-speed DVD+RW drives.

DVD RAM

DVD RAM format supported which makes this drive a Multi drive supporting CD, DVD Rom, DVD RAM.

Seamless Link

Seamless Link prevents loss of discs caused by writing errors

8.5GB storage capacity

Single sided double layer disc with 8.5 GB storage capacity

