

Philips  
External Drive

external

8x ReWriter

SPD400|CC



## Simply Superior Performance

Slim external DVD 8x rewriter G-base

With its superior performance, reliability and speed, the ultra-slim fits easily into your briefcase or laptop bag. Its elegant silver and black design looks sensational and is ideal for home or office use.

### Witness the latest technology

- 8.5GB storage capacity on a single sided double layer disc
- Double layer writer for +R and -R, DL media
- DVD RAM enlarging your storage capacity

### Superior Performance

- Fast recording of your (re)writable discs
- 4X writing speed on 8.5 GB double layer discs

### Extreme Reliability and Robustness

- Dynamic Calibration ensure writing quality at high DVD speed
- Safe and reliable rewriting with Seamless Link

### Convenience

- Dual Format
- Plug & Play for easier installation

**PHILIPS**  
sense and simplicity

## Specifications

### Writing Speed

- **CD-R:** 24X (3600KB/sec) by CAV
- **DVD+R:** 8X (10800KB/sec) by Z-CLV
- **DVD+R DL:** 4X (5400KB/sec) by CLV
- **DVD-R:** 8X (10800KB/sec) by Z-CLV
- **DVD-R DL:** 4X (5400KB/sec) by CLV
- **DVD-RW:** 5X

### Rewriting Speed

- **CD-RW:** 24X (3600KB/sec) by CAV
- **DVD+RW:** 8X (10800KB/sec) by ZCLV
- **DVD-RW:** 6X (8100KB/sec) by ZCLV

### Reading Speed

- **Access time:** 130ms
- **Buffer size:** 2MB
- **CD-R:** 24X (3600KB/sec) by CAV
- **DVD ROM:** 8X (10800KB/sec) by CLV
- **RAM:** 1X (1350KB/sec) by CAV

### Convenience

- **Ease of installation:** Plug & Play

### Power

- **Adaptor type:** AC
- **Power consumption:** 25 W W

### Technical specifications

- **Access time:** DVD: <140msec (typical)
- **EMC standards:** EN55022, EMS55024, FCC Part 15
- **Humidity:** 10 - 90 %RM (no condensation)
- **Safety standards:** EN60950, EN60825, UL1950
- **Storage temperature range:** -40 - 65 °C

### System Requirements

- **Hard disc space:** 650MB

- **PC OS:** Windows 98 SE, 2000, ME, XP
- **Processor:** Pentium 4 1.3GHz or Higher CPU
- **RAM memory:** 128MB

### Dimensions

- **Product dimensions (WxDxH):** 47x22.5x40
- **Product weight:** 9.1 kg

### Inner Carton

- **I2NC:** 867000028132
- **EAN/UPC/GTIN:** 8712581323202
- **Gross weight:** 0.1 kg
- **Height:** 187 mm
- **Length:** 102 mm
- **Quantity:** 1
- **Width:** 226 mm

### Outer Carton

- **I2NC:** 867000028132
- **EAN/UPC/GTIN:** 8712581323219
- **Height:** 47 mm
- **Length:** 22.5 mm
- **Quantity:** 8
- **Width:** 40 mm

### Outer Carton 2

- **Quantity:** 120

### Packaging Data

- **I2NC:** 867000028132
- **EAN/UPC/GTIN:** 8712581323202
- **Gross weight:** 0.17 kg
- **Height:** 187 mm
- **Length:** 102 mm
- **Width:** 226 mm

## Product highlights

### Dual format writer on +/- DL

New drive enabling writing on both +R and -R 8.5 GB double layer media

### DVD RAM

DVD RAM format supported which makes this drive a Multi drive supporting CD, DVD Rom, DVD RAM.

### Dynamic Calibration

Dynamic Calibration optimizes DVD writing quality of high-speed DVD+RW drives.

### Seamless Link

Seamless Link prevents loss of discs caused by writing errors



Date of issue 2007-02-27

Version: 2.0

I2 NC: 8670 000 30505  
EAN: 87 12581 33892 3

© 2007 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)